

Marine House, Marine Park, Gapton Hall Road, Great Yarmouth, NR31 ONB, United Kingdom

1000 Series Mini Beacon



1000 Series Mini Beacons incorporate Applied Acoustics' proprietary Sigma acoustic protocols, proven for use with AAE's USBL tracking systems, other manufacturers' USBL systems operating with wide bandwidth transmissions, as well as those using 'narrow band' tone signalling.

With an industry standard 5-pin connector, the beacons are quick and easy to configure using the 1082 Smart Switch or 1083 Multi-Charger that also activate and monitor the charging of the battery pack.

Key Features

- AAE proprietary Sigma bi-directional spread spectrum technology
- Quick and easy configuration
- Directional or omni-directional beam pattern options available
- Externally configurable as transponder, responder or pinger
- High power option model to operate longer ranges
- Options for use with remote transducers

Applications

- General purpose tracking and positioning applications
- Static and dynamic operations e.g. ROV, sidescan sonar.

Technical Specification

MODEL TYPES – PHYSICAL SPECIFICATION

Housing material: Hard anodised aluminium, with clear protection sleeve and stainless steel cage

	Beam Pattern	SPL*	Survival Depth	Diameter	Length	Weight in air
1015	±45°	194dB	2000m	74mm	410mm	3.08kg/1.46kg
1015H High Power	±30°	196dB	2000m	74mm	410mm	3.08kg/1.46kg
1019	±90°	188dB	1500m	74mm	395mm	2.88kg/1.38kg
1022	±20°	202dB	4000m	95mm	418mm	5.03kg/2.75kg

*Effective SPL is 5dB less when used with iXBlue GAPS USBL systems.

ELECTRICAL SPECIFICATION

Battery

Battery type Listening life Rechargeable. NiMH as standard 60 days



1000 Series Mini Beacon Technical specification continued...

Operational life, AAE Spread Spect	rum Dependent on pulse rate and operational mode 1015: 150 hours at 1.0pps 1015H: 100 hours at 1.0pps 1019: 150 hours at 1.0pps 1022: 100 hours at 1.0pps Operational life reduced when used with non AAE USBL systems.
Configuration	
Transmit frequency range Receive frequency range Turnaround time Transmit pulse width	24 - 33.5kHz 17 - 31kHz 15/30/60/100ms dependent on channel selection 1.5/3.0/10ms dependent on channel selection
External Inputs	
Connector type Responder key External power Charge	MCBH5M 5-way connector + 5 to 25 Volts 22 to 35 Vdc@80mA Onboard fast charger for 3 hour charge, typical. Activated and monitored via 1082 Smart Switch or 1083 Multi-Charger

USBL COMPATIBILITY

AAE 1000 Series beacons use Tone, Chirp, MFSK, DSSS and FHSS as transmission/reception protocols, allowing cross-compatibility with many USBL systems, including:

AAE Nexus	Spread Spectrum systems
AAE Easytrak	All models, tone systems
iXBlue	GAPS USBL
Kongsberg	HPR/HiPAP
ORE/Edgetech	USBL
Sonardyne	USBL

OPTIONS

Compatibility with USBL systems not listed above

Non-rechargeable batteries (alkaline)

Toroidal beam pattern version, Model 1019T

Survival depth to 4000m

Remote transducer (supplied with Model BCN-1010 electronic bottle); RM90, omni-directional rated to 1500m. RM45, directional, rated to 2000m. Inter connect cable, 2m standard

Depth sensors 100m/300m/1000m/2000m/4000m (adds D suffix to model number)

Digital depth transmission when used with AAE Nexus USBL systems

Floatation collar



Due to continual product improvement, specification information may be subject to change without notice. 1000 Series Mini Beacon/ March 2015 ©Applied Acoustic Engineering Ltd.



Applied Acoustic Engineering Ltd

T +44(0)1493 440355

(F) +44(0)1493 440720

general@appliedacoustics.com

www.appliedacoustics.com